


# **XLA-5 Series**

## Fast and compact linear actuator



The XLA micro linear actuators are world class in terms of weight, size and precision. The actuator is driven by the Crossfixx<sup>™</sup> ultrasonic piezo motor, allowing an extremely compact design, variable speeds up to 200 mm/s and a total weight of less than 36 gram! The XLA-5 has an integrated encoder with a 1250, 312 or 78 nm resolution or open-loop. A wide range of rod lengths is available, allowing stroke lengths from 10 mm to 300 mm! The open-loop version also comes with an integrated controller to make the whole setup even more compact.

#### **Key features**

	closed-loop	open-loop				
drive principle	patented Crossfixx™ ultrasonic piezo technology					
lifetime	> 1000 km / typ. 20 million cycles					
input voltage	12 to 48 V	12 V				
controller	XD-OEM controller required	integrated controller				

#### Model code structure

actuator type	rod length (mm)	encoder resolution (nm)	FPC cable outlet (flexible printed cable)			
	-45	-OPEN				
		-1250				
		-312				
		-78				
	-55					
	-65					
	-75					
XLA-5	-85		top side			
ALA-3	-105		top side			
	-125	same as XLA-5-40				
	-145					
	-285					
	-305					
	-325					

Example: **XLA-5-45-312** 

- XLA-5 series linear actuator
- Rod length of 45 mm
- Closed-loop actuator with integrated encoder with a resolution of 312 nm

### **Environmental compatibility**

temperature range	-30°C to +70°C
humidity range	20% to 90% RH (non-condensing)
heat dissipation (motor only)	< 5 W
internal operation voltage	< 60 V

### **Motion performance**

					XLA-5	all rod len	gths	unit	tolerance
				-1250	-312	-78	open-loop		
LIN	LIMITS type			mechanical		mechanical + magnetic			
		type	opti	cal, increme	ental				
ĒR		grating period		79.8		no encoder	μm		
ENCODER		resolution	1250	312	78	+ integrated	nm		
Ž		index		1	per full strol	ке	controller		
		accuracy			± 5			μm	typ.
	positioning	resolution = min. step size = min. incremental motion (MIM)		1250	350	80	20 – 50 μm (pulsed operation)	nm	typ.
	osit	unidirectional repeatability		± 1250	± 350	± 80		nm	typ.
œ	<u> </u>	bidirectional repeatability		± 2500	± 700	± 160		nm	typ.
ACTUATOR		max. speed		200		500	mm/s	typ.	
Ę		min. speed	2 to 5			10	μm/s	typ.	
¥	Speed	stability (at typical speed of 10 mm/s)			± 1	±1 -		%	typ.
		point-to-point positioning time for a 1 mm step*			25 40		-	msec	typ.
		point-to-point positioning time	10 mm 1 mm 100 µm	130 25 20				msec	typ.

### **Mechanical properties**

			XLA-5								unit	tolerance		
rod length		-45	-55	-65	-75	-95	105	-125	-145	-165	-185	-205	mm	± 0.1
dimensions	closed- loop		38 x 30 x 9.1									mm	± 0.1	
amonorono	open-loop					38	x 30 x 1	2					******	2 0.1
stroke / trave	10	20	30	40	60	70	90	110	130	150	170	mm	± 0.1	
mass	closed- loop	35.8	36.6	37.4	38.2	39.8	40.8	41.6	42.4	43.2	50	50.8	g	± 5%
mass	open-loop	37.0	37.8	38.6	39.4	50.8	51.2	52	52.8	53.6	54.4	55.2		
max. acceler	950	840	730	650	530	490	420	370	330	300	270	m/s <sup>2</sup>	typ.	
holding force	holding force 5						N							
driving force		5							N					
actuator materials aluminum (housing) steel rod and stainless steel housing cover														
cable type			Closed loop version: FPC, 12 core, 0.5 mm pitch with opposite side contacts Open loop version: FPC, 14 core, 0.5 mm pitch with opposite side contacts											

				XL	A-5			unit	tolerance		
rod length		-225	-245	-265	-285	-305	-325	mm	± 0.1		
dimensions	closed- loop		38 x 30 x 9.1								
difficitions	open-loop		38 x 30 x 12								
stroke / trave	l range	190	210	230	250	270	290	mm	± 0.1		
mass	closed- loop	51.6	52.4	53	53.8	54.6	55.4	g	± 5%		
mass	open-loop	56	56.8	57.6	58.4	59.2	60	9			
max. acceleration		250	220	210	200	180	170	m/s <sup>2</sup>	typ.		
holding force			N								
driving force 5							N				
actuator materials aluminum (housing) steel rod and stainless steel housing cover											
cable type		Closed loop version: FPC, 12 core, 0.5 mm pitch with opposite side contacts Open loop version: FPC, 14 core, 0.5 mm pitch with opposite side contacts									


#### Controller/software

The XLA-5  ${\bf closed\text{-}loop}$  actuators are compatible with the  ${\bf XD\text{-}OEM}$   ${\bf Controller}.$ 

The XLA-5 **open-loop** actuators have a **built-in controller**.

Controlling of the stage is done with:

- Easy-to-use Windows interface
- LabVIEW interface program (compiled program or source)
- MATLAB interface script
- C++ and Python libraries



Last updated: 4/03/2024s. All specifications are subject to change without prior notice.